

Seat Color
Black Vinyl

Body Colors
Blue
Red



LIGHTWEIGHT PORTABLE SCOOTER

Ride



3 wheel
GB-117

The next generation of the popular Buzzaround scooter series is now available! The 2015 Buzzaround XL offers more standard features to make your riding experience better than ever. Featuring a wraparound Delta tiller, a new LED battery gauge and a new LED angle-adjustable headlight, the new Buzzaround XL is longer to offer more foot room, with a great turning radius. The Buzzaround XL disassembles in seconds with just four easy steps making transporting it from one destination to another a breeze!

Rise. Roll. Ride.

GOLDEN
technologies

YOUR LIFE IN MOTION



LIGHTWEIGHT PORTABLE SCOOTER

3 wheel Specifications

Model	GB117
Medicare Code (pending)	K0800
Weight Capacity	300 lbs.
Drive Wheels	Rear
Maximum Speed	4 mph
Operating Range ¹	8 miles / 14 miles
Under Deck Clearance	3"
Turning Radius	37"
Type Batteries	2-12 AH / 2-22 AH
Colors	Red, Blue
Freewheel Mode	Yes
Electronic Speed Control	Yes
Electro-Mechanical Brakes	Yes
Charger	Off-board
Controller	50 Amp Dynamic R-Series
Dimensions	
Length	42.5"
Width	21.5"
Height (ground to top of back of seat)	33" -35"
Ground to Top of Seat	21" -23"
Ground to Top of Deck	4.75"
Deck to Top of Seat	16" -18"
Number of Seat Height Positions	3
Size of Increments	1"
Front Axle to Rear Axle	33.5"
Weight of Unit: (assembled) ³	101 lbs.
Front Half	35 lbs.
Rear Half	25 lbs.
Seat w/Arms	20 lbs.
Batteries	21 lbs / 31 lbs pack
Tires:	
Front	Solid 8"
Rear	Solid 8"
Rear Anti-Tippers	2"
Standard Seat	Stadium Style
Back Height - no headrest	16"
Width x Depth	17" x 16"
Color	Black Vinyl
Optional Seats:	Stadium Style
Back Height - no headrest	16"
Width x Depth	18" x 16", 20" x 18"
Color	Black Vinyl
Warranty:	
Frame	Lifetime Warranty
Drive Train	2 Year Warranty
Electronics ²	2 Year Warranty

¹ Battery range will vary due to rider weight, drive surface and terrain, battery charge, battery condition, battery type, and tire condition.

² Electronics warranty excludes batteries.

³ Assembled weight calculated with the standard battery pack 2-12 AH batteries.

Wireless disassembly in 4 easy steps!



Step 1: Pop off the seat!



Step 2: Pull out the battery pack!



Step 3: Fold down tiller and lock in place!



Step 4: Pull forward on the drivetrain release lever to separate the front and rear frame sections!



Disassembles into 5 pieces!

4 wheel model shown



A battery charging port is conveniently located on the tiller under the control panel.

Features

- 300 lb. weight capacity
- Tiller mounted basket
- Angle-adjustable LED headlight

Literature is current at time of printing. Golden Technologies reserves the right to make changes to the product or literature at any time.



Golden Technologies • 401 Bridge Street, Old Forge PA 18518 • Tel: (800) 624-6374 • Fax: (800) 628-5165 • www.goldentech.com

SHT-GB117-072715